



Child-Safe Manual Rollers - Easy Spring Series

Question	Answer
May 11, 2020	
This works for s45 and s60 systems?	There are 3 versions of the S45 tube, light, standard and heavy duty. (different wall thicknesses), The ESS works with all three S45 tubes. S60 tube has a larger diameter, 60mm. The ESS does not have adapters or components to fit that tube, therefore it does not work with the S60 tubes.
Compliant with new Canadian standards May 21?	Yes, The Easy Spring Series is compliant with the proposed regulation which is planned to go into effect, tentatively May 2021.
Do you have any tips/tricks for consistently adjusting the tension?	If the correct spring booster is selected for the sade, the spring will not lose its tension once it is set with the required pre-tension. If a spring is not holding its tension, it could be a sign that the spring is not apropriate for the application, a stronger booster may be required.